

# KOPkit

## Keep-On-Pumping kits that can save you time and money

When you need a part, you've got it! A KOPkit can help you cut downtime and put you back in business fast. Use KOPkits for preventative maintenance also, to ensure continuous high performance from your Pulsafeeder metering pump.

Save money too, by buying parts in KOPkits instead of ordering individual parts.

KOPkits are available for the CHEM-TECH Series 99X, Series 100, Series 200 and Series CTP; Mec-O-Matic Stingray Series and Dolphin Series; and all PULSAtron metering pumps.

### FOR DIAPHRAGM PUMPS:

A typical KOPkit includes Pump Head assembly with Valve, Diaphragm, Head Screws, Washers and an exploded view assembly drawing.

### FOR PERISTALTIC PUMPS:

A typical KOPkit includes Pump Head assembly with Tube, Retaining Clamps, Hose Clamps and an exploded view assembly drawing.

### HOW TO ORDER:

**PULSAtron (all models)** - The KOPkit number will start with the letter "K", followed by the head size (4th digit of the pump model number) and the liquid end code (the 7th, 8th, 9th and 10th digits of the pump model number). The KOPkit for pump model number LB04SA-PTC1-XXX would be K4PTC1.

**CHEM-TECH Series 99X, 100 & 200** - The Series 100 & 200 KOPkit number will start with "KX100-" followed by the liquid end code (the 7th, 8th, 9th and 10th digits of the pump model number). The KOPkit for pump model number X240-XD-BAAAXXX would be KX100-BAAA. The KOPkit for all Series 99X pumps is KX100-AAAA.

**CHEM-TECH Series CTP** - The KOPkit number will start with "NCK" followed by the 4th, 5th, 6th, 9th, 10th, 11th and 12th digits of the pump model number. The KOPkit for pump model number CTPD4HSA-PAP1-XXXXX is NCKD4HPAP1.

**Mec-O-Matic Stingray Series** - The KOPkit number for the Stingray Series is KUSR\_-BCAK with the 3rd digit of the pump model number placed in the blank spot. The KOPkit for pump model number US210XA-BCAKXXX is KUSR2-BCAK.

**Mec-O-Matic Dolphin Series** - The KOPkit number for the Stingray Series is KUDXX-L\_AU with the 8th digit of the pump model number placed in the blank spot. The KOPkit for pump model number UD50-XA-LSAUXXX is KUDXX-LSAU.



technology  
innovation diversity  
excellence