

PULSAtron®

Series E

Electronic Metering Pumps



Key Features

- **Manual Control** by on-line adjustable stroke rate and stroke length.
- **Agency approved** for demanding **OUTDOOR** and indoor applications.
- **Highly Reliable** timing circuit.
- **Water Resistant** excellent for **OUTDOOR** and indoor applications.
- **Internally Dampened To Reduce Noise**, very acceptable for household installations.
- **Guided Ball Check Valve Systems**, to reduce back flow and enhance outstanding priming characteristics.
- **Premium Standard Wetted Component Materials**.
- **Few Moving Parts** and **Wall Mountable**.
- **Safe & Easy Priming** with durable leak-free **bleed valve assembly** (standard).

Complete Economical Selection

Nineteen distinct models are available, having pressure capabilities to 300 PSIG @ 3 GPD, and flow capacities to 600 GPD @ 30PSIG, with a turndown ratio of 100:1. Metering performance is reproducible to within $\pm 3\%$ of maximum capacity.

Please refer to the reverse side for Series E specifications.

Operating Benefits

Reliable metering performance. Our guided check valves, with their state-of-the-art seat and ball designs, provide precise seating, and excellent priming and suction lift characteristics. Our timing circuit is highly reliable and, by design, virtually unaffected by temperature, EMI and other electrical disturbances.

Rated "hot" for continuous duty. Series E pumps continue to meet their specifications for pressure and capacity even during extended use. That's because of our high quality solenoid and special enclosure that effectively dissipates heat.

High viscosity capability. A straight flow path and ample clearance between the diaphragm and head enable standard PULSAtron pumps to handle viscous chemicals up to a viscosity of 3000 CPS. For higher viscosity applications, larger, spring-loaded connections are available.

Leak-free, sealless, liquid end. Our diaphragms are of superior construction—PTFE-faced, bonded to a composite of Hypalon and fabric layers, and reinforced with a metal insert for optimum flexibility and durability.

For additional information about PULSAtron's full-featured Series MP & Series E PLUS, refer to Technical Sheet No. EMP-027 & EMP-021, about the mid-range Series D & Series A PLUS refer to Technical Sheet No. EMP-023 & EMP-025. For information about the economical Series C PLUS & Series C, refer to Technical Sheet No. EMP-026 & EMP-024.

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

System Compatibility

A wide variety of chemicals can be pumped.

Liquid end materials include glass-filled polypropylene (GFPP), PVC, styrene-acrylonitrile (SAN), Polyvinylidene Fluoride (PVDF), PTFE, Hypalon, Viton, ceramic, alloys and 316SS.

Immediate installation and start-up.

Included as standard accessories with all models are an injection/back pressure valve assembly and a foot valve/strainer assembly*, including discharge and suction tubing (*not avail. with high viscosity connections for >3000 CPS).

Safe and easy priming and valve maintenance.

Included as a standard accessory is a bleed valve assembly, including return tubing (available only on those models with tubing connections and ≤ 240 GPD).

Quick and economical liquid end maintenance.

Available for every model is a unique KOPkit®, a convenient, economically priced, package containing new cartridge check valves and other important spare parts.



technology
innovation
diversity
excellence

PULSAtron Series E Specifications

Pressure and Flow Rate Capacity

MODEL	LEK2	LE12	LE02	LE33	LE13	LE03	LEK3	LEF4	LE34	LE14	LEE4	LEH4	LEG4	LE44	LEK5	LEH5	LEH6	LEK7	LEH7	LEJ7	LEH8	
Capacity	GPH	0.13	0.21	0.25	0.5	0.5	0.5	0.6	0.85	0.9	1	1.25	1.7	1.75	1.85	2.5	3.15	5	8	10	10	25
nominal	GPD	3	5	6	12	12	12	14	20	22	24	30	41	42	44	60	76	120	192	240	240	600
(max.)	LPH	0.5	0.8	0.9	1.9	1.9	1.9	2.3	3.2	3.4	3.8	4.7	6.4	6.6	7	9.5	11.9	18.9	30.3	37.9	37.9	94.6
Pressure	PSIG	300	250	150	250	150	100	100	250	150	100	150	250	150	100	150	150	100	50	35	80	30
(max.)	BAR	21	17	10	17	10	7	7	17	10	7	10	17	10	7	10	10	7	3.3	2.4	5.5	2
Connections	Tubing	1/4" ID X 3/8" OD 3/8" ID X 1/2" OD 3/16" ID X 5/16" OD														3/8" ID X 1/2" OD 1/2" ID X 3/4" OD (LPH8 ONLY)						
	Piping	1/4" FNPT														1/4" FNPT 1/2" FNPT						
Reproducibility at max. capacity		+/- 3%																				
Viscosity Max CPS		For viscosity up to 3000 CPS, select connection size 3, 4, B or C with 316SS ball material. Flow rate will determine connection/ball size. Greater than 3000 CPS require spring loaded ball checks. See Selection Guide for proper connection.																				
Stroke Frequency Max SPM		125																				
Stroke Frequency Turn-Down Ratio		10:01																				
Stroke Length Turn-Down Ratio		10:01																				
Power Input		115 VAC/50-60 HZ/1 ph 230 VAC/50-60 HZ/1 ph																				
Average Current Draw @ 115 VAC		1																				
@ 230 VAC		0.5																				
Peak Input Power Watts		300																				
Average Input Power @ max SPM: Watts		130																				


Important: Series E - 19 model selections. Digit 1 and 2 (LE) signify product class, digit 3 and 4 signify pressure/flow. For full model selection information refer to Price Schedule EMP-PS LP.

Liquid End Materials

Series	Pump Head	Diaphragm	Check Valves		Fittings	Bleed Valve	Injection Valve Assembly Foot Valve Assembly	Tubing
			Seats/O-Rings	Balls				
E	GFPPL PVC SAN PVDF 316 SS	PTFE-faced Hypalon-backed	PTFE, Hypalon, Viton	Ceramic, PTFE, 316SS, Alloy C	GFPPL PVC PVDF	Same as fitting and check valve selected, except 316SS	Same as fitting and check valve selected	Clear PVC White PE

Important: Material Code— GFPPL = Glass-filled Polypropylene, PVC = Polyvinyl Chloride, SAN = Styrene-Acrylonitrile, PE = Polyethylene, PVDF = Polyvinylidene Fluoride. hypalon and Viton are registered trademarks of E.I. DuPont Company. PVC wetted end recommended for sodium hypochlorite.

Dimensions



Series E Dimensions (inches)																	
Model No.	A	B	B1	C	C1	D	E	Shpg Wt	Model No.	A	B	B1	C	C1	D	E	Shpg Wt
LE02	5	9.6	-	9.5	-	6.4	8.2	7	LEH4	6.2	10.9	-	11.2	-	8.2	9.5	18
LE03	5	9.8	-	9.5	-	6.4	8.4	7	LEH5	6.2	11.3	-	11.2	-	8.2	9.9	18
LE12	5	9.6	-	9.5	-	6.4	8.2	7	LEH6	6.2	11.3	-	11.2	-	8.2	9.9	18
LE13	5	9.8	-	9.5	-	6.4	8.4	7	LEH7	6.1	11.7	-	11.2	-	8.2	10.3	18
LE14	5	9.8	-	9.5	-	6.4	8.4	7	LEH8*	6.1	-	10.9	-	10.6	8.2	-	23
LE33	5.4	10.6	-	11.2	-	7.5	9.2	12	LEK2	5.4	10.3	-	10.8	-	7.5	8.9	10
LE34	5.4	10.6	-	11.2	-	7.5	9.2	12	LEK3	5.4	10.6	-	10.7	-	7.5	9.2	10
LE44	5.4	10.6	-	11.2	-	7.5	9.2	12	LEK5	5.4	10.9	-	11.7	-	7.5	9.5	15
LEF4	5.4	10.6	-	11.7	-	7.5	9.2	15	LEK7	6.1	11.7	-	11.2	-	8.2	10.3	18
LEG4	5.4	10.6	-	11.7	-	7.5	9.2	15	LEJ7	6.1	10.0	-	10.7	-	-	-	18

NOTE: Inches X 2.54 = cm

* the LPH8 is designed without a bleed valve available



An ISO Certified Company



Brochure No. EMP-022
Printed in the USA J/07



A Unit of IDEX Corporation

NOVA-TECH
INTERNATIONAL

800 Rockmead Dr Ste 102 • Houston, TX 77339-2496
Tel: (281) 359-8538 • Toll Free Tel: (866) 433-6682
Fax: (281) 359-0084 • Toll Free Fax: (866) 433-6684
sales@novatech-usa.com • www.novatech-usa.com