

# POLARTRONIC N-Series

## Automatic Polarimeters



### Features

- Continuous, Exceptionally-Fast Measurements
- Electronic Interface Of Analyzer And Optical Encoder For Extreme Precision
- No Primary Moving Parts For Ultimate Service Life
- Accuracy Of  $\pm 0.01^\circ$  Throughout Entire Measuring Range
- Wide Selection Of Sample Cells
- Flow-Through Measurement w/ Specialized Sample Cells
- Backlit LCD
- American & European Pharmacopoeia Conformance
- GLP/GMP Conformance

**SCHMIDT + HAENSCH**

Opto-Electronic Measuring Instruments Since 1864



## POLARTRONIC N-Series Automatic Polarimeters

The S+H POLARTRONIC Automatic Polarimeters are truly in a class by themselves. Their measurement speed and accuracy are unmatched in the industry.

Polarimeters, by definition, determine the optical activity of a solution by means of a rotating analyzer and an optical encoder. S+H POLARTRONIC Automatic Polarimeters make use of a (S+H patented) direct, electronic interface between the analyzer and the optical encoder. This technique allows for exceptional speed in measurements and consistent accuracy across the entire measuring range. All other manufacturers employ mechanical linking of the analyzer and optical encoder. This results in much slower measuring time, inconsistent accuracy across the measurement range, and shortened service life due to mechanical wear and tear.

S+H N-Series Automatic Polarimeters feature accuracy of  $\pm 0.01^\circ$ . Instruments are available in single and multiple wavelength configurations. All models come standard with halogen light sources, backlit LCD displays, password protection, printer and data ports, & optional USB ports.

A wide selection of S+H samples cells and quartz control plates are also available.

Schmidt+Haensch has been manufacturing precision opto-electronic instruments since 1864. All S+H instruments are manufactured in Germany.

Go with a name you can trust for the highest level in analytical instrumentation...choose Schmidt+Haensch.



## Technical Specifications

	NH38	NHX	NW2
Cat. No.	46101	46103	46105
Measuring Scale:	$^\circ$ Arc	$^\circ$ Arc	$^\circ$ Arc
Measuring Range:	$\pm 85^\circ$	$\pm 85^\circ$	$\pm 85^\circ$
Resolution:	0.01	0.01	0.01
Accuracy:	$\pm 0.01$	$\pm 0.01$	$\pm 0.01$
Optical Wavelength(s) (STANDARD):	589nm	589nm	589nm
Optical Wavelength(s) (OPTIONAL):	N/A	546nm, 478nm, or 633nm, (Selection Of 1)	N/A
<small>NOTE: Optional wavelengths provided at no additional charges.</small>			
Wavelength Selection:	N/A	Manual	Automatic
Measuring Light Source:	Halogen	Halogen	Sodium
Analyzer/Optical Encoder Link:	Electronic	Electronic	Electronic
Measuring Time:	< 3.0 Sec.	< 3.0 Sec.	< 3.0 Sec.
Sensor:	Hi-Res CCD	Hi-Res CCD	Hi-Res CCD
Sample Cell Length (Maximum):	200mm	200mm	200mm
Zero Calibration:	Air / Empty Sample Cell	Air / Empty Sample Cell	Air / Empty Sample Cell
Display:	LCD, 1x16 Characters	LCD, 1x16 Characters	LCD, 1x16 Characters
Keypad:	4-Key	4-Key	4-Key
Password Protection:	Yes	Yes	Yes
Languages:	English & German	English & German	English & German
Printer Interface:	Centronics (Parallel)	Centronics (Parallel)	Centronics (Parallel)
Computer Port:	RS-232C	RS-232C	RS-232C
USB Port:	Optional	Optional	Optional
Power Requirements:	90-240V AC, 50/60Hz	90-240V AC, 50/60Hz	90-240V AC, 50/60Hz
Dimensions:	735 x 425 x 200mm	735 x 425 x 200mm	735 x 425 x 200mm
Weight:	28.0kg	28.0kg	28.0kg
Manufactured In:	Germany	Germany	Germany

## Applications...

Quality Control Of Original, Intermediate, & Final Products ● Determination Of Concentration & Purity Control ● Purity Control & Substance Concentration Determination Conforming To U.S. & European Pharmacopeia Standards ● Analysis Of Sugar & Albumin In Urine ● Hormone/Enzymology/Toxicology Research ● Purity Control & Identity Of Essential Oils ● Purity Control & Determination Of Organic Fluids & Inorganic Ions ● Analysis Of Optically Active Compounds ● Determination Of Configuration Changes Of Macromolecules In Solutions

## NOVA-TECH INTERNATIONAL

800 Rockmead Dr Ste 102 • Houston, TX 77339-2112  
Tel: (281) 359-8538 or (866) 433-6682  
Fax: (281) 359-0084 or (866) 433-6684  
sales@novatech-usa.com • www.novatech-usa.com

## Markets...

Food ● Beverage ● Sugar ● Clinical ● Medical ● Pharmaceutical ● Cosmetic ● Chemical

### Please refer to our additional brochures for the following:

S+H VISPOL-Series Manual Polarimeters  
S+H UniPol-L Automatic Polarimeter  
S+H POLARTRONIC M-Series Automatic Polarimeters/Saccharimeters  
S+H POLARTRONIC H-Series Automatic Polarimeters  
S+H SACCHAROMAT Automatic Saccharimeters  
S+H Purity Analyzers  
S+H AutoFilt Semi-Automatic Pressure Filtration System  
S+H Sample Cells & Quartz Control Plates